

fufonk

I akk/kr jk"Vh; ; {ek fu; æ.k dk; Bæ ds vrxr I Hkh 38 ftyk ; {ek dñka , oajkt; ds iR; d
 i kFked LokLF; dñns ij cyxe tkp grqiz, Dr yxHkx 800 ckbukdyj ekbdkt dki ds okf"kd
 j [k&j [kko ½ Annual Maintenance Contract½ grq, d o"z dsfy, fuekz kdUkkz @ vf?kdr ifr"Bku l s
 nj fu/kkj.k grqvYi dkyhu fufonk vkef=r dh tkrh gA fu/kkZjr frfFk ds i'pkr-ikr fufonk
 Lohck; ZughagkskA fufonk [kkyrs l e; fufonknkrk Loā @ ikf/kdr ifrfuf/k mifLFkr jg l drsgA
 bPNd fufonknkrk l hycm iLrko fucd/kr Mkd@LiHM ikkV }kjk iF"kr djxkA
 fufonk tek djus dh vāre frfFk% 07-12-09 3 P.M
 fufonk tek djus , oā [kkyus dk LFkku& jkt; LokLF; l febr] fcgkj] 'k[kij] i Vuk
 fufonk [kkyus dh frfFk , oā l e; % 07-12-09 3%0 P.M

fu; e , oā 'kukz

- 1- fufonk ds l kfk : 0 5000-00 ¼ kpb gtkj½ ek= dk cfd MRV tks jkt; LokLF; l febr] fcgkj
 dsuke nš gskk] l ayXu djuk vko'; d gā
- 2- fufonk nkrk dks v/kru vk; dj , oafcdh dj pdrk iek.k i= l ayXu djuk gtxkA
- 3- fufonknkrk dks i s uā , oā oV uā dh Nk; k ifr l ayXu djuk vko'; d gskkA
- 4- fufonk i i= eā vādr nj ds vrfjDr fdl h idkj dk vl; Hkqrku nš ughagkskA
- 5- ok; ukdyj ekbdkt dki dh eJefr @ nš [kj] k iR; d rhu ekg ij ftyk ; {ek dñns ij rFk
 iR; d N% ekg ij l Hkh ikFked LokLF; dñns ij fd; k tk; skA
- 6- fufonk ds vākr% ; k iwkz% jnā @ LFfXr djus dk iwkz vf/kdkj v/kkz Lrk{kjh dk l jf{kr
 jgskA
- 7- oškfud ekeyka ds fu"i knu grqU; kf; d {ks= i Vuk gskkA
- 8- fufonknkrk dks ck; ukdyj ekbdkt dki ds fuEu Accessories dk nj fuekz kdriz dā uh dsuke
 l fgr vādr djuk gskkA

Sl. No.	Specification and technical details of parts
1.	Power cord/On-off switch/bulb holder (any of these)
2.	6V/20-21 W halogen lamp-High lumen, bright light-imported
3.	Power supply unit(complete)-New electric system
4.	Power supply unit-Repairing-spare parts kit of electric system.
5.	Eye piece-ISI mark, ISO 9001-2000 Co.-Extra Wide field
6.	10X Objective-ISI mark, ISO 9001-2000Co.
7.	40X Objective-ISI mark, ISO 9001-2000Co
8.	100X Objective-New-ISI mark, ISO, 9001-2000 Co.
9.	100X Objective-Rejuvenation-Inner lens assembly kit of 100X
10.	Prism assembly/head unit-New head
11.	Prism assembly/head unit-Repairing-Parts kit of head unit
12.	Complete stage assembly-New ball bearing based M/C stage
13.	Complete stage assembly-Repairing-Parts kit of stage assembly.
14.	Filter element-Blue/White/Transparent filter imported
15.	Filter element-Condenser-new
16.	Coarse and find movement drive combined-New
17.	Coarse and fine movement drive combined-Parts
18.	Reflector mirror with stand and arch complete assembly
19.	Eye guard, imported to protect eyes from electric shocks.
20.	Microscope Maintains book/Laminated chart/lens clearing spray